



**Frank Bacon Machinery Sales Co.**  
21251 Ryan Road  
Warren, MI 48091  
586-756-4280 [www.frankbacon.com](http://www.frankbacon.com) Email: [sales@frankbacon.com](mailto:sales@frankbacon.com)

Stock #	DESCRIPTION
13269-08	<p>Thermotron ATS-320-V-10-705-LN2 Thermal Shock Chamber (1) Used Thermotron, Model ATS-320-V-10-705-LN2 hermal Shock Chamber. S/N 23727 <a href="#">Click to View OEM Brochure</a> <b>Thermotron Model ATS-320-V-10-705-LN2</b></p> <p><b>SPECIFICATIONS:</b> <b>Product Carrier Dimensions:</b> 25"W x 15"D x 15"H <b>Temperature Range:</b> <b>Hot Chamber:</b> +60°C to +200°C <b>Cold Chamber:</b> -73°C to +177°C <b>Overall Exterior Dimensions :</b> 75"W x 73"D x 105"H <b>Approximate Weight:</b> 3,800 lbs. <b>Electrical Requirements:</b> 460V/60Hz/3Ph/121A <b>MFG Date:</b> 12-8-1999 (Upgraded to New Thermotron 8825 Programmer/Controller) <b>Performance:</b> To MIL-STD 883, Method 1010.7, MIL-STD 202, Method 107G and Many Other Automotive and Electronic Thermal Shock Specifications. <b>Maximum Loading (Mechanical Refrigeration):</b> -55C to 85C: 80 lbs -65C to 150C: 35 lbs <b>Maximum Loading (LN2 Assist):</b> -65C to 200C: 80 lbs MIL-STD 883 1010.7 Test Load (-65C to 150C): 30 lbs</p> <p><b>EQUIPPED WITH:</b></p> <ul style="list-style-type: none"><li>• Stainless Steel Interior</li><li>• Refrigeration Service Taps</li><li>• Door Safety Interlocks</li><li>• <b>Thermotron 8825</b> Programmable Touch Screen Controller</li><li>• Fully Programmable, Monitor or Control Chamber from any Computer, Tablet or Smart Phone</li><li>• Optional LN2 Assist for Lower Temperature Range: -73C to 177C in Cold/Hot Chamber and 60C to 200C in Hot Zone</li><li>• Users Manual</li></ul> <p><b>FOB Warren, MI</b> <b>Condition: Excellent</b> <b>30 Day Satisfaction Guaranteed Return Privilege</b></p> <p>* Actual Images</p>

**Guarantee:** Unless otherwise specified, every machine is offered with the standard **MDNA** (*MACHINERY DEALERS NATIONAL ASSOCIATION*) Return privilege to ensure your complete satisfaction. If the machine is un-satisfactory it may be returned to our warehouse, freight prepaid and in the original condition within 30 Days of shipment for a full refund less the cost of SPECIALIZED EQUIPMENT, NEW ITEMS AND RE-CERTIFICATION COSTS, When applicable. Care is taken to provide accurate specifications. However, Critical areas should be verified by Inspection.